

Fax 860-496-9017 www.waringcommercialproducts.com

Illustration#	Part#	Description	
1	028769-E	Eastman Jar Lid Cover	
2	035238-V	Vinyl Jar Lid	
3	035465	Blending Asssembly (with O ring and bearing holder nut)	
4	035239	48 oz. Stackable Container ONLY	
5	035885 035091	Jar Pad (changed after 8/2/2018) Jar Pad (use 035885)	
6	035085	Hole Plug (4 required)	
7	034275	Sems (4 required)	
8	034273	B Gasket (4 required)	
9	037034 035251	Drive Coupling Machined (on units after 9/19/2019) Drive Coupling	
9a	037033	Coupling Washer (on units after 9/19/2019)	
10	503460-160	Top Housing Assembly	
11	035237	Control Housing Back Bezel	
12	035162	TBB160 Control Panel Assembly	
13	035253	LED Lens	
14	035090	Screw (4 required)	
15	034900	PCB Cushion (2 required)	
16	013604	Washer (2 required)	
17	034904	Rubber Pad (2 required)	
18	034902	Sems (2 required)	
19	034272	A Gasket (4 required)	
20	034274	Screw (4 required)	
21	034276	ECM Motor / KB500	
22	012409	Small Crimp Connectors (2 required on units after 11/22/2016) (4 required)	
	019123	Large Crimp Connector (2 required on units after 11/22/2016) (1 required)	
23	013731	Cable Ties (6 required on units after 11/22/2016) - (2 required)	
24	503483	Motor Housing with Dampeners	
25	035124 026925	Cordset (on units after 4/25/2016) Cordset	
26	033619 007556	Strain Relief (on units after 4/25/2016) Strain Relief	

Illustration #	Part #	Description
27	503480 035079	Bottom Housing & Feet Bottom Housing ONLY
28	034274	Screw (4 required)
29	035088	Foot (4 required)



